

PCI-8™: 8-Channel Acoustic Emission System on a Board

The PCI-8 "AE System on a Board" provides 8 channels of simultaneous waveforms and AE features. This new digital data acquisition AE system resides on a full-size PCI card and is very cost effective. Through the high performance PCI bus and Direct Memory Access (DMA) architecture, significant AE data transfer speeds can be attained (up to 132 Mb/sec.), assuring a wide bandwidth bus for multi-channel AE data acquisition and waveform transfer. Digital acquisition circuitry virtually eliminates drift, thereby achieving high accuracy and reliability.

PCI-8™ AE Subsystem boards occupy one full-size PCI slot in a computer chassis and can be implemented inside most standard PC computers or inside one of PAC's four (4) rugged, multichannel PAC SAMOS™ (Sensor based Acoustic Multichannel Operation System) system chassis, which include SAMOS-112/48/32 and µSAMOS™. Due to advances in surface mount technology and high density FPCA's devices, PAC has been able to provide this single AE System on a Board with 8 complete high speed, AE channels of acquisition waveform processing and transfer, 2 analog parametric input channels and 8 digital input and output control signals.



µSAMOS™ Chassis for up to 24 Channels of AE



PCI-8™ AE System on a Board

Key Features

- Low power consumption.
- 8 digital (16-bit A/D) complete AE channels on one full-size PCI card.
- PCI-bus provides AE data transfer rates of up to 132
 Mb/sec to a PC computer.
- 4 High Pass, 4 Low Pass filter selections for each channel, totally under software control.
- Up to 2 parametrics on each PCI-8 board with update rates up to 10,000 readings/second (when attached to hit data).
- Designed with multiple FPGA's and ASIC IC's, to provide extreme high performance and minimize components and cost.
- Hit LED drivers are built within the PCI-8 board so that AE activity LED's can be attached directly.
- Built-in AE feature extraction provides high speed transient data analysis at high hit rates.
- Built in waveform processing with DMA & Bus Mastering transfer for high speed transfer of waveforms on all 8 AE channels.
- Digital signal processing circuitry virtually eliminates drift, thereby achieving high accuracy and reliability.

PCI-8™ Board Sample Specifications:_

Physical Specifications:

• Size: 13.415" L x 4.8" H x 0.7" T

Weight: 1.1 lbs.

• Power Consumption: 10 Watts (w/o Preamps)

• DC Power: +12.0 volts, 0.4 amps

-12.0 volts, 0.1 amps +5.0 volts, 1.0amp

Electrical Specifications:

AE Inputs: 8 channelsInput Impedance: 50 Ohms

• **Preamplifier Power:** 28V Phantom Power

Power & Signal on Coxial

Connection

Sensor Testing: AST built-inFrequency Response: 1 kHz - 400 kHz

(at -3 dB points)

Signal Processing:

• AE Signal Gain: 0, 6 dB computer selectable

• Filters: 4 High Pass computer

selectable filters - 1 kHz, 5.0 kHz, 20 kHz, 100 kHz, 4th order Butterworth 4 Low Pass computer selectable filters - 50 kHz,

100 kHz, 200 kHz, 400 kHz,

4th order Butterworth

• Max. Signal Amplitude: Up to 100 dB AE

Up to 99 dB ASL

• ADC Type: 16 bit, 3MSPS per channel

maximum

• Waveform Sample Rate: Computer selectable

100 kSPS, 200 kSPS, 500 kSPS,

1MSPS, 3MSPS

• Extracted AE Features: Time of 1st Threshold Cross-

ing, Time to Peak, Peak Amplitude, Envelope Strength, Duration, Rise Time, Counts, True Energy, RMS, ASL, Parametric 1 & 2 **Analog Parametrics:**

Parametric Channels: 2

Parametric A/D Res.: 16 bits

• Parametric Sample Rate: 10 kHz sample rate for each

analog parametric

• Time Driven Data Rate: Controlled by software

10 msec. to 60 seconds

• Time Parametrics: All parametrics are available

in time data set

Additional I/O:

• Digital I/O: 8 Digital Inputs

8 Digital Outputs

• Audio Monitor Interface: Analog switch and buffer to


select desire channels to be routed to PAC audio monitor

board

• LED Activity Monitor: On board LED driver to

directly drive LED's on front panel. LED minimum on time

is 0.05 seconds



SAMOS-32 System for up to 32 Channels of AE



195 Clarksville Road, Princeton Junction, NJ 08550 USA Phone: (609) 716-4000 • Fax: (609) 716-0706

Email: sales.systems@mistrasgroup.com • www.mistrasgroup.com